

Engravings	1.50	1.53	1.59	1.60	1.67	1.74
LC MEDIA 5/8	O50	O53	O59	O60	O67	O74



A = LC Media 5    B = LC Media 8    R = Right Eye    L = Left Eye

**Centering:** Center the lens according to the monocular distance PD and make sure that the marking line overlaps the center of the pupil when looking straight in horizontal (zero) distance direction.

**Required ordering data:** Measured prescription for distance refraction and the choice of required vertical support level LC Media 5/8.



LC Media 5/8 are enhanced, everyday single vision lenses; however, they should be blocked and finished similar to progressive lenses.

## LC MEDIA 5/8



Engravings	1.50	1.53	1.59	1.60	1.67	1.74
LC COMPU 40 / 60	P50	P53	P59	P60	P67	P74

## LC COMPU 40 / 60



Minimum Fitting Height = 18mm

